National Line Card | Canada

Products & Systems Solutions







Approach

Our goal is to deliver the outcomes that matter most to you—from more comfortable indoor environments to energy efficient operations. We take a consultative approach to understand your unique business objectives, gather data and information to make informed recommendations, and support you from implementation to validation.

Service & Solutions

Our capabilities include commercial systems, energy services & solutions, contracting, controls/building automation, rentals and service.



Building Services

Help reduce operating costs and extend the life of your equipment with planned, reliable, preventative and proactive scheduled maintenance and repair by Trane factory trained technicians.

- Service Agreements - Connected Mechanical Service Agreements
- Extended Warranty
- Quoted Repair Products



Digital Services

Leverage your data and Trane's analytics to create simple dashboards that can help you to understand performance of your building and its assets. Dashboards can help to find opportunities for increasing efficiency, decreasing energy use, and increasing productivity through system optimization.

- Connected Building Service
- Agreements
- Secure remote access and building management with TraneConnect[™]
- Trane® Autonomous Control

Intelligent Services

Trane Intelligent Services provides oneon-one consultative support to reduce energy use, manage operational costs, and optimize building performance. Take the guesswork out of understanding building data to achieve more comfortable spaces while meeting your financial and environmental goals.



Rental Services

- 24/7/365 local service, engineering expertise and an expansive fleet of rental products. Promptly provides temporary, scalable HVAC and power from standard applications to complex solutions
- Water-Cooled Chillers, Air-Cooled Chillers, Temporary Power, Cooling Towers, Packaged A/C Units, Air Handlers, Portable A/C Units

IAQ Services



Today there are more ways than ever to assess and manage indoor air quality, while keeping your goals for cost and sustainability in sight. Trane offers a variety of services, innovative technologies, and proven solutions for measuring and monitoring IAQ. We can help you align with air quality guidelines and recommendations set by the CDC, EPA, and ASHRAE.

Trane Creative Solutions

Customized Trane Equipment Modifications Including: Multizone Replacements, Water-Side Economizer Coils for Air-Cooled Chillers, Packaged Air-Cooled Ice Storage Systems, Acoustical Attenuation

Engineer and Contractor Resources

Trane is here to support, enable and educate Engineers and Contractors through comprehensive tools and resources, design and analysis tools, professional education and training, BIM and CAD drawings, and pre-engineered system solutions.

traneengineer.com | tranecontractors.com



- Comprehensive Chilled Water Systems
- Comprehensive Chiller- Heater Systems
 CoolSense® Integrated Outdoor Systems
- Geothermal Systems
- Intelligent Variable Air Systems
- Thermal Battery[™] Systems
- Zoned Rooftop Systems

Energy Services



Trane enables more efficient, sustainable buildings by providing a single source for decarbonization and modernization solutions, programmatic implementation services, and financing and funding options. We use deep expertise and a data driven approach to understand how energy impacts your unique situation, and collaborate to develop strategies to deliver your goals for carbon reduction, resiliency, and energy optimization.

Energy Solutions include:

Building modernization and automation |Lighting | Water Conservation | Renewables and Distributed Energy Resources | Funding, financing, and procurement programs

Trane is accredited by NAESCO as an Energy Services Provider (ESP), a U.S. DOE-qualified Energy Services Company (ESCO), and recognized by the Canadian Federal Buildings Initiative as a qualified bidder.



Building Automation



Tracer[®] SC+

Scalable building automation system solution with standard, open protocols



Pivot® Smart Thermostat Wi-Fi & Ethernet thermostat for light commercial applications

2-

Symbio[®] Application Specific and Programmable Unit Controllers, Integrates with BACnet MSTP. BACnet/IP, BACnet/Zigbee, Lontalk & Modbus Protocols



Air-Fi[®] Zone Sensors Flexible and reliable wireless sensors & system communications leveraging Air-Fi[®] Wireless (BACnet/Zigbee) technology. Sensors include temperature, humidity, CO2 & occupancy

Building Management Systems



Tracer[®] Ensemble[®] Enterprise level building management software for facility professionals

	-	_	
		R.	-
ē I		2	-9
	1.11	2	-
_	_	2	2

Tracer[®] Synchrony[®] Tracer SC+'s built-in web based user interface software for building operators



and simple user interface for nontechnical users **BAS Operator and Occupant**

Light commercial control system

with set-up wizard for installers

Apps Providing mobile access to service providers, building operators, and occupants

Tracer[®] Concierge[®]



Trane® Autonomous Control Al-based solution that performs automatic system optimization using real-time weather data and predictions, building occupancy trends & energy usage patterns

IAQ Solutions



Synexis Best in class air purification and surface cleanliness by creating Dry Hydrogen Peroxide from naturally occurring oxygen and humidity in the air to significantly reduce many different pathogens.



TCACS Trane Catalytic Air Cleaning System (TCACS) is an enhanced air filter containing 3 technologies: filtration, ultraviolet light, and a photocatalytic oxidation (PCO) process

Data Center Cooling



Performance Climate Changer[®] for Data Centers Maintains tight temperature and humidity tolerances for server room environments.

Oil-free; Cooling operation;

100-250 Tons; 400-600 Tons.

CenTraVac® Model CVHE

and Cooling capable; Free

CenTraVac® Model CVHF

200 - 500 Tons: R-514A

3-Stage Compressor: Heating

Cooling; Symbio® 800 controller;

2-Stage Compressor; Heating and

Heat recovery operation; Symbio®

800 controller; 325 - 2000 Tons;

Cooling capable; Free Cooling;

Model TACW

R-134a and R-513A

Water-Cooled **Centrifugal Chillers**













R-514A

Multi-Stage Dual Compressor; Heating and Cooling capable; Free Cooling; Symbio[®] 800 controller; 1450 - 3950 Tons; R-514A

CenTraVac® Model CDHH Multi-stage; Dual Compressor; Heating and Cooling capable; Free Cooling; Symbio® 800 controller; 1800 - 4000 Tons; R-1233zd

Water-Cooled Chillers



Cold Generator™ Model CGWR Scroll Compressors; 20 - 75 Tons; R-410A

Series R[®] Model RTWD Helical Rotary Compressor; Heating and Cooling capable; Heat recovery operation-dual setpoint; Up to 165°F HW production; Symbio[®] 800 controller: 80 - 250 Tons: R-513A and R-515B



Series R[®] Model RTHD **Optional Variable Speed Helical** Rotary Compressor; Heating and Cooling Capable; Symbio® 800 controller; 175 - 400 tons; R-513A

Air-Cooled Chillers



Ascend[®] Air-to-Water Heat Pump Model ACX Energy efficient, all electric heating and cooling; Symbio[®] 800 controller; 140-230 tons cooling; 1500 - 2500 MBh heating; R-454B



Ascend[®] Model ACS Scroll Compressor; 140 - 230 Tons; R-454B; Heat recovery; Symbio[®] 800 controller



Ascend[®] Model ACR Variable Speed Helical Rotary Compressor; Free Cooling; Symbio[®] 800 controller; 150 - 550 Tons; R-513A



Model CGAM Scroll Compressor; 20 - 130 Tons: R-454B: Heat recovery option; Symbio[®] 800 controller

Model TCAA Oil Free Centrifugal; 60 - 440 Tons; R-513A



Sintesis[®] Model RTAF Variable Speed Helical Rotary Compressor; 115 - 500 Tons; R-513A; Symbio[®] 800 controller

Cold Generator™ Model CCAR Scroll Compressor with Air-Cooled Condenser; 20 - 70 Tons

Industrial Process Cooling



TAEevo TECH Air-cooled process chiller; Indoor and outdoor use; 1-50 Tons; R-410a



ARIES TECH2 Air-cooled process chiller; Outdoor use; 60-200 Tons; R-410a

Modular Units



Thermafit[®] Model AMC Air-Cooled Chiller; Optional Free-Cooling, Heat Recovery Up to 140°F (60°C); 15-80T Modules (1 - 12 Modules per Bank); R-454B



Thermafit® Model MWC Water-Cooled Chiller; Optional Heat Recovery Up to 180°F*; 15-80T Modules (1 - 12 Modules per Bank); R-454B; R-513*





CenTraVac® Model CVHH Multi-stage compressor; Heating and Cooling capable; Free Cooling; Heat recovery

CenTraVac[®] Model CDHF

operation, Symbio[®] 800 controller; 900 - 2000 Tons;



Thermafit[®] Model MAR Split Chiller with Remote Condenser; 15-80T Modules (1 -12 Modules per Bank); R-454B



Thermafit[®] Model AXM Air-to-Water Heat Pump Vapor Injection Compressors; Up to 140°F (60°C) 30T Modules; 374 MBH (2 - 12 Modules per Bank); R-454R



Thermafit® Model WXM Water-to-Water Heat Pump; Up to 140°F (60°C) 20-80T Modules; 262-1033 MBH (1 - 12 Modules per Bank); R-454B



Thermafit® Model MWS Water-Source Multi-pipe; Up to 140°F (60°C)30-60T Modules; 432-942 MBH (3 - 10 Modules per Bank); R-454B



Thermafit® Model MAS Air-Source Multi-pipe; Vapor Injection Compressors; Up to 140°F (60°C); 30T Modules; 433 MBH (3 - 10 Modules per Bank); R-454B



Thermafit[®] Model TACW Water-cooled chiller; Oil-free centrifugal; 60 - 135 Tons (1000 Ton Banks); R-513A



Cold Generator[®] Model CICD Water-cooled; Heat Recovery; 20 - 85 Ton (600 ton Arrays)

Thermal Storage



Thermal Energy Storage Tanks Helps manage peak electric

demand for buildings with chilled water heating and cooling systems above 100 tons. Optimizes energy usage and lowers operating costs by storing and leveraging renewable, excess, or inexpensive energy.



Thermal Battery™ **Air-Cooled Chiller Plant**

Pre-Engineered, Factory Built Cooling System. Incl: Air-Cooled Chillers, CALMAC® Energy Storage Tanks, Customizable System



Thermal Battery[™] Storage-Source Heat Pump System Delivers Heating and Cooling, Supports Electrification. Incl: Water-to-Water and Air-to-Water Heat Pumps, CALMAC® Energy Storage Tanks, Trane Controls

Packaged Units



Impack[®] Cooling, Gas/Electric, Heat Pump & Dua I-Fuel; Multiple Efficiency Levels; Up to 16 SEER; (1 ph-15 SEER2); 2 - 5 Tons



Foundation® Cooling, Gas/Electric; Adapts to Competitors Roof Curbs; 3 - 25 Tons

Precedent[®] &

Precedent[®] with eFlex[™] 3 - 25 Tons; Cooling, Gas, Electric, Heat Pump & Hybrid Dual Fuel; Standard, High, & eFlex Ultra-High Efficiency (up to 25.4 IEER); Symbio 700 control with Mobile App and Air-Fi® capable

Zoned Rooftop Systems Pre-designed for small building comfort: Includes Precedent or Voyager rooftop unit, VAV terminal units, Tracer[®] Concierge[™] system control & Air-Fi® wireless controls & sensors; 3 - 50 Tons

Voyager[®] 3

Cooling, Gas/Electric; eStage™ Multi-Staged Compressors; Full & part load efficiencies; Symbio 700 and Mobile App; Up to 17.5 IEER; 27.5 - 50 Tons

IntelliPak® 1

Cooling, Gas/Electric, Hot Water; 20 - 130 Tons (Available with eFlex[™] Variable Speed Compressor: 20 - 75 Tons). Symbio 800 Controller with 7" Touchscreen Display, Air-Fi® Capable; up to 19 IEER

IntelliPak® 2



Cooling, Gas/Electric, Hot Water, Air-Cooled; 90 - 150 Tons, Available with eFlex[™] Variable Speed Compressor, Standard Double Wall Foam, Symbio 800 Controller with 7" Touchscreen Display, Air-Fi® Capable; Up to 19.3 IEER

IntelliPak® 3



Tons, Available with eFlex™ Variable Speed Compressor. Standard Double Wall Foam, Symbio 800 Controller with 7" Touchscreen Display, Air-Fi® Capable, Up to 17.8 IEER

Trane Thrive (OAXX) Indoor Agriculture packaged product (DX, Air and Water Cooled); Heat Pump, Gas, and Hot Water; 3-80 Tons

Self-Contained Units



Water-Cooled Self-Contained Model SWUD Single-piece units ideal for new construction market; Redesigned with upgraded features; Symbio 500 controller with TD7; R-454B; Up to 22.8 IEER; 20-110 Tons

Contained System Smallest Footprint on the Market; Water-Cooled System; Variable speed compressors and fans; Industry-leading Part Load Efficiency - Up to 20.8 IEER; 25 - 80 Tons, cassette construction

Water-Source Heat Pumps



Axiom[™] Standard **Efficiency Model GEH/GEV** Horizontal (0.5 - 15T) or vertical (0.5 - 25T); Deluxe sound option for quiet operation; Multiple airflow configurations; 0.5 - 25 Tons

Single-Stage Model EXH/EXV

sound option for quiet operation:

Horizontal or vertical; Deluxe

Motor (ECM); Rotary or scroll

Electronically Commuted

compressor; 0.75 - 6 Tons

Axiom Variable Speed

Model VSH/VSV

Axiom High Efficiency





Axiom High Efficiency Two-Stage Model DXH/DXV Horizontal or vertical; 2-Stage compressor; Deluxe sound option for quiet operation; Meets LEED EAc4 requirement; 2 - 6 Tons





Console Model GEC ASHRAE 62 indoor air quality compliant; Quiet operation; 0.5 - 1.5 Tons



Model GET Multiple capacities & cabinet sizes; Available in PSC or ECM motors; Flexible air supply options; Integrated controls; 0.75 - 3 Tons

Axiom Vertical Stack



Axiom Water-to-Water Model EXW Co-axial heat exchanger; Rackable modular design; 5, 10, 20 Tons

Axiom Rooftop



Air Handling Units



Performance Climate Changer[®] - Catalog Dependable performance at an uncompromising value; Compact Footprint; Factory-Engineered, Mounted & Tested Controls; Indoor/Outdoor; Up to 15000 CFM; 2" R-13 Construction









Modular Self-



Performance Climate Changer[®] - Semi-custom (CSAA/PSCA) Leading Efficiency and Casing

Performance: Dimensional Flexibility enabling Easy Installation: Indoor/Outdoor; Up to 60000 CFM; up to +/-10 in w.g.; 2", R-13 or 3", R-19 Construction; Factory Engineered, Mounted & Tested Controls



Performance Climate Changer - Custom (TCFS/TCPA) Now available in side-by-side configurations; Indoor or outdoor; Unlimited dimensional flexibility and airflow; Up to +/- 12 in. w.g. operating pressure, with <1/2% air leakage rate; Absolute thermal barrier with performance up to R-25



Trane Air Rotation Unit Indoor or Outdoor; Up to 300 tons and 120,000+ CFM; CW or DX; 2" Foam Insulated panels, factory engineered & mounted controls

Make-Up Air Gas Heating Units



Model GSAA Indoor Gas-Fired Make-Up Air Handlers; Standard & High Efficiency; 100 - 1200 MBH



Model GRAA Outdoor Gas-Fired Make-Up Air Handlers; 100 - 1200 MBH

Model AHOA Packaged Air Handlers; Cooling, Make-Up Air, & Ventilation

Unit Heaters



Gas Fired Unit Heaters 14 sizes, from 30 to 400 MBh; 409 stainless steel; Single point power; Direct Spark ignition; Tubular heat exchangers; OSHA fan guard



Electric Unit Heaters Model UHWA/UHAA/UHRA/

UHXA/UHEC/UHCA 7 styles, over 200 configurations; Sized from 1.5 to 50 kW; Capacities from 5 to 16.4 MBh; Vertical or horizontal discharge: Single point power; UL Listed



Hydronic Unit Heaters Model UHS/UHP 38 unit sizes from 8 to 720 MBh; Vertical and horizontal configurations; 2-point or 4-point installation; Single point power: Steam or hot water; OSHA fan

guard; ETL/ETLc certified



High Efficiency Gas Fired Unit Heater Model HINA/HIPA 6 sizes: 50-400MBH, natural and LP gas. 3:1 self-modulating turndown; >95% Efficiency

Terminal Units



Blower Coil Blower Coil Model BCXE; Indoor; Up to 4000 CFM; Horizontal and Vertical Configurations; ECM Motors, Multiple Filter Options, Factory-Engineered & Mounted Controls

CoolSense® Terminal Unit Up to 1300 CFM; Variable speed ECM ; Symbio[®] 500 controller (available with Air-Fi wireless)

VariTrane[®] Model VC*F Single Duct Variable Air Volume Boxes; 25 - 8000 CFM; Optional Factory Installed Piping Package

VariTrane[®] Model VDDF **Dual Duct Variable Air Volume** Boxes; 80 - 8000 CFM



Parallel Configuration Fan-Powered Variable Air Volume Boxes; 200 - 2200 CFM

VariTrane[®] Model VS*G Series Configuration Fan-Powered Variable Air Volume Boxes; 200 - 2500 CFM; optional integral suppressor attenuator available

VariTrane® Model L**F Low Height Fan-Powered Variable Air Volume Boxes: 100 - 1800 CFM; Parallel or Series Configuration



VariTrane[®] Model VRRF Round Inlet/Round Outlet RetroFit Variable Air Volume Boxes; 25 - 4000 CFM



UniTrane[®] Model FC*B Horizontal or Vertical Fan Coil; Cabinet, Recessed or Compact Configurations; 200 - 1200 CFM



Force-Flo™ Model FF*B Horizontal or Vertical Cabinet Heater; Concealed or Recessed Configurations; 200 - 1200 CFM

Model VUVE Vertical Unit Ventilators; 750 - 1500 CFM

Model HUVC Horizontal Unit Ventilators; 750 - 2000 CFM

Split Systems



Split Systems Cooling & Heat Pump; Gas, Electric, or Hot Water Heat; 1.5 - 5 Tons



Odyssey™ Symbio® 700 controller ; Full & part load efficiencies; Up to 14.8 IEER; 6 - 25 Tons



Air-Cooled Condensing Units; Available with Remote Chiller Evaporators; 20 - 120 Tons



CAUJ Air-Cooled Condensers; 20 - 120 Tons

Outdoor Air Solutions

RAUJ



Horizon[®] DOAS (OAXX) DOAS; Packaged product (DX, Air and Water Cooled); Heat Pump, Gas, and Hot Water; >43°F Dew Point capability: ERV; AHRI 920 rated; 3-80 Tons

Up to 100% outdoor air; Packaged

product (DX - Gas Heating); >51°F

Dew Point capability; ERV; AHRI

340/360 certified; ASHRAE 90.1

Horizon[®] Flex[™] (HAXX)

compliant; 10 - 15 Tons





TR150/TR200

Trane Variable Frequency Drives; 6, 12, 18 Pulse



Trane - by Trane Technologies (NYSE: TT), a global climate innovator - creates comfortable, energy efficient indoor environments through a broad portfolio of heating, ventilating and air conditioning systems and controls, services, parts and supply. For more information, please visit trane.com or tranetechnologies.com.

All trademarks referenced in this document are the trademarks of their respective owners.

© 2024 Trane. All Rights Reserved.

EDU-SLB048-EN 09/06/2024



