







80% GAS FURNACES



Every Trane 80% furnace delivers an Annual Fuel Utilization Efficiency (AFUE) of 80%, exceeding federal government standards for furnace efficiency. This means that 80% of the energy you pay for is converted into heat that keeps your home comfortable no matter what the weather's like outside.

PREMIER		80 Two-Stage Variable Speed Gas Furnace Formerly S8V2-C 80% AFUE	
		80 Single-Stage Variable Speed Ultra-Low Nox Gas Furnace Formerly L8V1 80% AFUE	
PRIORITY		80 Two-Stage Gas Furnace Formerly S8X2 80% AFUE	
		80 Single-Stage Gas Furnace Formerly S8X1 80% AFUE	
CHOICE		80 Single-Stage Builder-Grade Gas Furnace Formerly S8B1 80% AFUE	

TRANE® LINK TECHNOLOGY FOR OPTIMAL PERFORMANCE.

Trane's communicating 80% gas furnaces are designed to deliver premium indoor comfort with precise control over temperature, humidity and air quality. On our 80 Two-Stage Variable Speed Gas Furnace our advanced Trane Link communicating technology seamlessly connects each of your system's components, allowing for advanced diagnostics, system performance updates, and optional remote monitoring that can help keep your system running at optimal performance levels throughout its lifetime.

MULTIPLE OPTIONS FOR EFFICIENT HEATING.

Trane's 80% two-stage gas furnaces offer an ideal blend of comfort and efficiency by adjusting fuel usage and run times to deliver just the right amount of heat. With these adjustments, you'll experience enhanced comfort, reduced temperature swings, and lower energy bills. Meanwhile, Trane's 80% single-stage gas furnaces provide an affordable option with the durable components you expect from the Trane brand.



Select models include innovative Trane Link technology, which uses Bluetooth to communicate between system components. Simply opt in through the Trane Home app to have your system's data remotely monitored for even the slightest system changes—letting you relax and enjoy the exceptional comfort your variable speed system provides.

**WE FREEZE.
BROIL.
STRESS.
DROP.
SHOCK.
EXPOSE.
LISTEN.**

SEET® TESTED

Every Trane system is put through some of the most extreme conditions found in nature in our SEET [System Extreme Environmental Test] lab. Put through five years of severe wear and tear in just a few months, our products can stand up to the harshest environments imaginable.



**AMERICA'S MOST TRUSTED® HVAC BRAND
10 CONSECUTIVE YEARS¹**



**MOST RELIABLE HEATING AND COOLING
EQUIPMENT BRAND²**

¹Trane received the highest numerical score in the proprietary Lifestory Research 2015-2024 America's Most Trusted® HVAC Brand studies. Study results are based on experiences and perceptions of people surveyed. Your experiences may vary. Visit www.lifestoryresearch.com.

²Trane Technologies Marketing Insights. Trane Brand Consumer Survey. June 2021.

150°

**WE'RE NOT
THE ONLY
ONES
TALKING
ABOUT
RELIABILITY.**

A CLOSER LOOK

Silicon Nitride Hot Surface Igniter

Provides a highly reliable ignition system for longer service life.

Multi-Port In-Shot Burners


Perfectly shape the flame cone for the maximum heat possible while using less fuel.

Two-Stage Gas Valve

Adjusts fuel use based on your heating demand, providing more comfort with lower, longer run times and reduced temperature swings.

Trane Link Communicating Capability

Creates a seamless connection between system components to monitor system performance and efficiency - helping deliver optimal comfort.



Premier 80

Aluminized Steel Heat Exchanger

Has a reliable design that resists corrosion, efficiently transfers heat, and is backed by a 20 year warranty.

Two-Speed Draft Inducer

Works seamlessly with the two-stage gas valve to enhance efficiency, comfort and reliability.

High Efficiency Variable Speed Blower Motor

Quietly distributes heat throughout your home while carefully controlling humidity levels by utilizing Comfort-R technology to regulate airspeed.

Vortica™ II Blower

Is quiet and efficient in both heating season and cooling season, and is only available from Trane.

The Premier 80 shown are for illustration purposes only. Please note that features and components may vary by model. As part of our continuous product improvement, Trane reserves the right to change specifications and design without notice.

FEATURES

	Premier	Priority		Choice	
	80 Two-Stage Variable Speed	80 Single-Stage Variable Speed Ultra-Low Nox	80 Two-Stage	80 Single-Stage	80 Single-Stage Builder-Grade
Annual Fuel Utilization Efficiency (AFUE)	80%	80%	80%	80%	80%
Trane Link Communicating Connectivity	Link	—	—	—	—
Communicating User Interface	✓	—	—	—	—
Variable-Speed Blower Motor	✓	✓	—	—	—
Comfort-R™ Humidity Control	✓	✓	—	—	—
Two-Stage Heat	✓	—	✓	—	—
Meets 14 ng/J NOx Requirement	—	✓	—	—	—
High Efficiency Constant Torque ECM Blower Motor	—	—	✓	✓	✓
Exclusive Vortica™ II Blower Housing Design	✓	✓	✓	✓	✓
Compatible with Two-Stage Outdoor Units	✓	✓	✓	✓	—
Insulated Blower Compartment*	✓	✓	✓	✓	—
Silicon Nitride Hot Surface Igniter	✓	✓	✓	✓	✓
Durable, Aluminized Steel Heat Exchanger	✓	✓	✓	✓	✓
Self-Diagnostic Integrated Furnace Control	✓	✓	✓	✓	✓
Heavy Gauge, Painted Steel Cabinet	✓	✓	✓	✓	✓
Compatible with Trane CleanEffects® Models	✓	✓	✓	✓	✓
Limited Lifetime Heat Exchanger Warranty with registration ¹	✓	✓	—	—	—
20 Year Heat Exchanger Warranty with registration ¹	—	—	✓	✓	✓
10 Year Limited Parts Warranty with registration ¹	✓	✓	✓	✓	✓

*14.5" models do not contain blower compartment insulation.

¹ Registered Limited Warranty terms are available when you register within 60 days of installation. You can register online at Trane.com or by phone at 855-260-2975, otherwise Trane's Base Limited Warranty terms will apply. Base Limited Warranty information on specific products can be found on Trane.com. Ask your dealer for full warranty information at time of purchase. Warranties are for residential and multi-family use only, some exclusions may apply. Product Registration and Registration Transfer exclusions vary in the US from state to state and in Canada from province to province. To determine if there are specific exclusions for your state or province check your local laws.

TRANE DEALERS ARE AS HARD TO STOP AS A TRANE ITSELF.

Independent Trane dealers take great pride in creating your perfect indoor environment. They are some of the most highly trained professionals in the business—with an extensive understanding of the movement and conditioning of air and the expertise to recommend, install and maintain the right system for your home.



WE ARE COMMITTED TO USING ENVIRONMENTALLY FRIENDLY PRINTING PRACTICES.



COMFORT. CONTROL. EFFICIENCY.

Optimize the comfort and efficiency of your home with the Trane Home smart comfort system.

The Trane Home mobile app gives you remote access to your HVAC system through your connected Trane smart thermostat. Adjust your temperature, set your schedule, and view your HVAC usage from anywhere.



Trane Home connects to your Trane HVAC system to provide you with remote control and diagnostics. To view additional integrations and subscriptions, visit our Knowledge Base at Trane.com/residential/home-subscription/

WHY IS INDOOR AIR QUALITY IMPORTANT?

We spend 90% of our time indoors, and 70% of that is in our home¹ where the air can be up to 5X poorer quality than the air outside². To help improve your indoor air, Trane offers a complete portfolio of air filtration equipment for whole home solutions for new and existing units.



TRANE CLEANEFFECTS® AIR CLEANER

Utilizes patented technology to deliver cleaner air to the whole home by removing up to 99.98% of airborne particles³ that pass through the re-usable filter, including 99.9% of the Influenza A (H1N1) virus⁴. This level of filtration makes it up to 100X more effective than a standard 1" filter⁵. Plus, it's the ONLY whole-home electronic air cleaner that is certified **asthma & allergy friendly**⁶ by the Asthma & Allergy Foundation of America.

Trane CleanEffects® is verified zero ozone producing so you can breathe easier knowing your air is free from harmful byproducts.⁶



ENERGY RECOVERY VENTILATORS (ERV)

Provide an energy-efficient way to exchange air inside your home with fresh air from outside, removing lingering odors like cooking smells while improving overall air quality.



HUMIDIFIERS AND DEHUMIDIFIERS

Deliver the right amount of moisture to the air throughout your home, adjusting from summer to winter.

Contact your Dealer or visit Trane.com/Residential to learn more.

¹The National Human Activity Pattern Survey (2001) | ²U.S. Environmental Protection Agency. EPA/600/6-87/002a. (1987)

³Based on 3rd party testing of particle removal efficiency down to 0.3 microns (2005)

⁴As reported by airmid healthgroup in ASCR092142v2 (2015) | ⁵Assuming <1% removal rate of 0.3-10 micron particles

⁶Verified Zero Ozone per UL 2998, Intertek certificate #Z0Z-90113-2023c



It's Hard To Stop A Trane.®

All trademarks referenced are the trademarks of their respective owners.

About Trane

Trane – by Trane Technologies (NYSE: TT), a global climate innovator – creates comfortable, energy-efficient indoor environments for commercial and residential applications. For more information, visit Trane.com or TraneTechnologies.com

© 2024 TRANE. ALL RIGHTS RESERVED. 72-1215-L-31 06/24